

Unter Haßlen 20 · D-78532 Tuttlingen
Phone: +49 (0)7462/9470-0
Fax: +49 (0)7462/9470-50
e-mail: sales@rz-medizintechnik.com
http://www.rz-medizintechnik.com




UROLOGY

Continuous Flow Laser Cystoscopy



THE PERFECT LASER CYSTOSCOPY SET



| 253-804-030 RZ Rod Lens Cystoscope, autoclavable, 4.0mm \varnothing , 30° direction of view




| 253-870-023 High Continuous Flow Laser Cystoscope Sheath, 23 Charr. including sheath and blunt obturator.



| 253-872-000 Telescope bridge and laser guide with 1 working channel for 8 Charr. laser fibers and instruments



| 253-873-000 Visual Obturator for easy insertion of the sheath into the urethra and bladder



LATEST TECHNOLOGY FOR OPTIMUM PERFORMANCE



State-of-the-art technology

High Continuous Flow Laser Cystoscope Sheath with telescope bridge and laser guide.



Safe and easy sealing

Rubber caps seal and keep the laser fibers in place.



Perfect visibility

For easy insertion of the sheath into the urethra and bladder

The new RZ high continuous flow cystoscope offers the surgeon a high-grade and reliable system for laser fibres to make cystoscopy safer and easier during diagnostic and practical surgery. It is the ideal solution to use in urethra, prostate and bladder or in every continuous flow operation.

- The 23 Fr. sheath with smooth, rounded tip allows easy and atraumatic inflow through the urinary tract
- With the large 8 Fr. working channel almost every catheter and instrument can be used as well as most side firing laser probes
- Our high continuous flow design keeps field view clear and simultaneous cooling when Laser is in use
- Latest RZ Optical technology provides a crystal-clear 30° scope that offers optimal brightness and clarity
- The effective tip design protects laser fibers from accidental tissue contact. It also minimizes obstruction of view with detaining bubbles or particulate emissions